

# HAND-HELD EYE SHOWERS




## MATERIALS WITH MEDIA CONTACT

Plastics: PA, POM, TPE  
 Metals: SS, AISI 316  
 Rubber: EPDM

## SAFETY

- Improved trigger lock
- Improved activation of the shower
- BROEB-LAB recommends the installation of a Thermostatic Mixing Valve (TMV) with safety shower equipment for safe operation, see page 11



## OPERATION

- Stay-open dust cap
- Light weight
- Well-balanced construction
- Spray pattern



## RELIABILITY

- Easy-to-clean spray head
- Anti-limescale design and material
- Improved functionality
- Long lifetime



reddot design award  
 winner 2013



## Eye Shower with Two 45° Heads



No. 27 10 009 10 05 011

Weight: Approx. 0.5 kg

Table mounted eye shower with two 45° angled heads, incl. 1.5m inlet hose. Trigger operated including a built-in check valve and FLOWFIX for regulation of water flow (14 l/min). Min. working pressure: 1,5 bar.

